



Available in T- style or Inline configurations and offered in lengths from 5 through 40 inches.

Sanitary clamp closures are a proven design suited for high purity beverage, chemical and pharmaceutical applications.

They are manufactured in 316L Stainless Steel with a 25 RA internal finish. All CSH housings are standard with 226 style cartridge adaptors allowing a positive locking tab seal.

Allows flexibility in one housing to use different cartridge lengths and maximise filter performance and cost.

Each housing has no internal threaded parts that come in contact with process fluid and is standard with food grade silicon gaskets.

1" sanitary gauge port tops with 1/2" sanitary vent and drain ferrules are standard features. Each vent and drain port are standard with solid cap, silicon gasket and clamp.

Maximum Operating Parameters

Maximum Pressure: 150 PSI (10 bar)

Maximum Operating Temperature: 230°F (110°C)

Standard Specifications

This is to give you an overview of our standard product, please see options on reverse with ordering information.

Model	Number Round	Length of Cartridge	Inlet / Outlet	Drains	Gauge Port With Vent	Max Ctg Diameter	Gaskets	Mounting Legs	Cartridge Seal 2-226 / Tabs
CSHI15	1	5"	1 1/2" TC	1/2" TC	Vent 1/2" TC	2 3/4"	Silicone	NA	Yes
CSHI11	1	10"	1 1/2" TC	1/2" TC	Vent 1/2" TC	2 3/4"	Silicone	NA	Yes
CSHI12	1	20"	1 1/2" TC	1/2" TC	Vent 1/2" TC	2 3/4"	Silicone	NA	Yes
CSHI13	1	30"	1 1/2" TC	1/2" TC	Vent 1/2" TC	2 3/4"	Silicone	NA	Yes
CSHI14	1	40"	1 1/2" TC	1/2" TC	Vent 1/2" TC	2 3/4"	Silicone	NA	Yes
CSHT15	1	5"	1" TC	1/2" TC	1 " TC / 1/2" TC	2 3/4"	Silicone	Yes	Yes
CSHT11	1	10"	1" TC	1/2" TC	1 " TC / 1/2" TC	2 3/4"	Silicone	Yes	Yes
CSHT12	1	20"	1" TC	1/2" TC	1 " TC / 1/2" TC	2 3/4"	Silicone	Yes	Yes
CSHT13	1	30"	1" TC	1/2" TC	1 " TC / 1/2" TC	2 3/4"	Silicone	Yes	Yes
CSHT14	1	40"	1" TC	1/2" TC	1 " TC / 1/2" TC	2 3/4"	Silicone	Yes	Yes

Filtrex Technology Pte Ltd

* 4009 Ang Mo Kio Ave 10, #04-37 TECHplace 1, Singapore 569738

| +65 6456 2388 | 7 : +65 6456 8266

Email : info@filtrex-tech.com | Website : www.filtrex-tech.com

Vent & Drain Twist Valve Option




Total Performance



Ordering Information

The housing catalogue number is made up of several variable characters i.e. Housing style, length, cartridge style, gasket material and others below. For example: a 1 round, T-style, 30" length, clamp closure, 316L SS, 2-226 seal, 1" ferrules, with legs, 25 RA internal finish with Silicon gasket would be designated as: CSHT13C6B11AS



Note:

Please contact Critical Process Filtration for other options or special requirements.

(Dimensions) Complete and detailed line drawings are available upon request. Please contact Critical Process Filtration with the model number and specifications you require.